






LOC		DIST		REVISIONS						
AF		50		P	LTR	DESCRIPTION		DATE	DWN	APVD
					D1	ECR-15-005665		10AUG2015	BDA	PKS

- 1
- SLOT TERMINATES A SINGLE MAGNET WIRE ONLY.
COPPER RANGE: 0.57-0.81mm [#23-#20] AWG.
ALUMINUM RANGE: 0.72-0.91mm [#21-#19] AWG.
ALUMINUM WIRE RANGE APPLIES FOR POST-TIN
PLATED VERSIONS ONLY.
- 2
- CONTINUOUS STRIP ON REELS WITH TERMINALS
LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 3
- BEND TO BE MADE AFTER TERMINAL IS INSERTED
INTO CAVITY AND MUST BE SECURELY HELD IN
CAVITY TO PREVENT PULL OUT.
- 4?
- DIMNESION APPLIES WHEN LEAF EDGE TOUCHES
CARRIER SIDE OF BOX



63899-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 12/APR/96	STE TE connectivity	
DIMENSIONS: mm [INCHES]		CHK RICHARD GRZYBOWSKI 15/APR/96	NAME	
		APVD GARY D. PORTA 24/APR/96	TERMINAL, TAB, 3.18[.125], MAG-MATE™	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-2012		
0 PLC ±-		APPLICATION SPEC 114-2046	SIZE A1	CAGE CODE 00779
1 PLC ±-			DRAWING NO C-63899	
2 PLC ±0.25[.010]			SCALE 10:1	
3 PLC ±-			SHEET 1 OF 1	
4 PLC ±-			REV D1	
ANGLES ±4°				
FINISH 0.002032 [.000080] MIN TIN PER MIL-1-10727		WEIGHT -	CUSTOMER DRAWING	