


RECOMMENDED P.C. BOARD LAYOUT

.010	0.25	.055	1.40	.220	5.59	—	—
.008	0.20	.043	1.09	.210	5.33	—	—
.005	0.13	.037	0.94	.165	4.19	—	—
.003	0.08	.030	0.76	.150	3.81	.950	24.13
.000050	0.00127	.020	0.51	.110	2.79	.620	15.75
.000030	0.00076	.015	0.38	.063	1.60	.530	13.46
IN	MM	IN	MM	IN	MM	IN	MM

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. HUFFMAN 28 APR 98	TE Connectivity	
DIMENSIONS: INCHES		CHK R. SWING 28 APR 98	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. REDDICK 28 APR 98	PRODUCT SPEC	
0. PLC ± —		APPLICATION SPEC		
1. PLC ± —		WEIGHT		
2. PLC ± —		—		
3. PLC ± .005		—		
4. PLC ± —		—		
ANGLES ± ° 30'		—		
FINISH SEE TABLE		—		
MATERIAL	8	CUSTOMER DRAWING		

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	640503	—

SCALE	SHEET	OF	REV
4:1	1	1	T