






REVISIONS					
P	LTR	DESCRIPTION	DATE	DNW	APVD
M2		REVISED PER ECR-21-118222	21JUL2022	JP	VS




- PARTS COMPLY WITH TE SOLDERABILITY SPECIFICATION 109-11-3.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- PRELIMINARY PART. NOT RELEASED FOR PRODUCTION.
- DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.




RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57 [0.062] THICK P.C. BOARD



SECTION A-A SCALE 10:1



3-DIMENSIONAL MODEL NTS



PHOSPHOR BRONZE, PRE-TIN	NYLON,UL94V-0,RED	641828-2
PHOSPHOR BRONZE, PRE-TIN	NYLON,UL94V-0,WHITE	641828-1
PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL	PART NO.

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T. BECK 12-3-93	TE Connectivity	
DIMENSIONS: INCHES		CHK R. SWING 12-3-93	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. SELF 12-14-93	PRODUCT SPEC	
0. PLC ± -	1. PLC ± -	108-1053		
2. PLC ± 0.13 [0.005]	3. PLC ± -	APPLICATION SPEC		
4. PLC ANGLES ± -	FINISH SEE TABLE	SIZE CAGE CODE DRAWING NO	RESTRICTED TO	
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT	A1 00779 C=641828	1
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 of 1	REV M2