



- 1 MATERIAL: CONNECTOR - NYLON UL94-V2 (WHITE)
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD 0.00203[.000080] MIN. THICK
FOR CONTACTS 644512-2 THRU 2-644512-8.
MATTE WHISKER MITIGATED TIN PLATE 0.00203[.000080] MIN. THICK
OVER NICKEL UNDERPLATE FOR CONTACTS 3-644512-2 THRU
5-644512-8.
- 2. CONTACTS ACCEPT 24 AWG WIRE WITH 1.52 [.060] MAXIMUM INSULATION DIAMETER.
- 3. CONTACTS MUST ACCEPT 0.64±0.03 [.025±.001] SQUARE POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6. HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP AND POLARIZING TAB.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 8 OBSOLETE PARTS



LEAD FREE	71.12 [2.800]	28	5-644512-8
	68.58 [2.700]	27	5-644512-7
	66.04 [2.600]	26	5-644512-6
	63.50 [2.500]	25	5-644512-5
	60.96 [2.400]	24	5-644512-4
	58.42 [2.300]	23	5-644512-3
	55.88 [2.200]	22	5-644512-2
	53.34 [2.100]	21	5-644512-1
	50.80 [2.000]	20	5-644512-0
	48.26 [1.900]	19	4-644512-9
	45.72 [1.800]	18	4-644512-8
	43.18 [1.700]	17	4-644512-7
	40.64 [1.600]	16	4-644512-6
	38.10 [1.500]	15	4-644512-5
	35.56 [1.400]	14	4-644512-4
	33.02 [1.300]	13	4-644512-3
	30.48 [1.200]	12	4-644512-2
	27.94 [1.100]	11	4-644512-1
	25.40 [1.000]	10	4-644512-0
DIM A	NO.OF POSN	ASSEMBLY	

CONTAINS LEAD	71.12 [2.800]	28	2-644512-8
	68.58 [2.700]	27	2-644512-7
	66.04 [2.600]	26	2-644512-6
	63.50 [2.500]	25	2-644512-5
	60.96 [2.400]	24	2-644512-4
	58.42 [2.300]	23	2-644512-3
	55.88 [2.200]	22	2-644512-2
	53.34 [2.100]	21	2-644512-1
	50.80 [2.000]	20	2-644512-0
	48.26 [1.900]	19	1-644512-9
	45.72 [1.800]	18	1-644512-8
	43.18 [1.700]	17	1-644512-7
	40.64 [1.600]	16	1-644512-6
	38.10 [1.500]	15	1-644512-5
	35.56 [1.400]	14	1-644512-4
	33.02 [1.300]	13	1-644512-3
	30.48 [1.200]	12	1-644512-2
	27.94 [1.100]	11	1-644512-1
	25.40 [1.000]	10	1-644512-0
DIM A	NO.OF POSN	ASSEMBLY	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN S. HOOVER 10-DEC-2004	APVD D. ROSSI 10-DEC-2004	NAME
0 PLC ±	1 PLC ±	2 PLC ±	3 PLC ±	4 PLC ±
ANGLES ±				
MATERIAL	FINISH	SIZE	CAGE CODE	DRAWING NO
		A1	00779	644512
CUSTOMER DRAWING		SCALE	SHEET	REV
		5:1	1 of 1	

STE TE Connectivity

MTA-100 CONNECTOR ASSEMBLY, 24 AWG, TAPE MOUNTED, STANDARD