




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
1		REV PER OSI5-0022-05	13APR2005	RG	MP



- 1 "AMP", PART NUMBER, AND DATE CODE TO BE MARKED IN AREA SHOWN
PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES
- 2 MATERIAL: HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, UL94 V-0
SIGNAL CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL
AREA OF POWER AND SIGNAL CONTACTS
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 6 PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES
- 7 PCB - .0453 ± .0010 DRILLED HOLES PLATED WITH .0003 MIN Sn OVER
.001 TO .003 CU PLATING TO ACHIEVE A .040 ± .003 DIA HOLE



PROPOSAL ONLY

2P + 12S	6450542-7
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.GRZYBOWSKI 13APR05	TE Connectivity	
DIMENSIONS:		CHK M.PERCHERKE 13APR05		
INCHES		APVD M.PERCHERKE -	NAME	
		PRODUCT SPEC	VERTICAL RECEPTACLE ASSEMBLY WITH GUIDES MULTI-BEAM XL	
		108-1973		
		APPLICATION SPEC		
		114-13038		
MATERIAL		WEIGHT	SIZE A 1	RESTRICTED TO
FINISH		-	CAGE CODE -	REV 1
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 2	REV 1

