


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W	REVISED PER ECR-24-213591	28JUN2024	RK	FJS

D

C

B

A



- 1 BRASS PER ASTM B-36.
- 2 $2.54\mu\text{m}$ [.000100] MIN TIN-LEAD OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL.
- 3 SELECTIVELY PLATED $0.76\mu\text{m}$ [.000030] MIN PRECIOUS METAL PLATE, FOR A DISTANCE OF 5.08 [.200] FROM MATING END, GOLD FLASH ON REMAINDER, ALL OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).
- 4 GOLD PLATING NOT TO APPEAR ON INSULATION SUPPORT STABILIZER.
- 5 POST WILL ACCEPT (SEE TABLE) TERMINATIONS.
- 6 .000100 MIN TIN OVER .000050 NICKEL. (POST).
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

OBSOLETE	6	3	SPECIAL	35.03 [1.379]	14.86 [.585]	1-66471-9
		3	1	37.97 [1.495]	17.81 [.701]	1-66471-8
		6	3	49.89 [1.964]	29.74 [1.171]	1-66471-7
OBSOLETE	6	6	1	37.97 [1.495]	17.81 [.701]	1-66471-6
		3	3	49.89 [1.964]	29.74 [1.171]	1-66471-5
		3	SPECIAL	35.03 [1.379]	14.86 [.585]	7 1-66471-4
OBSOLETE	2	2	SPECIAL	40.79 [1.606]	20.65 [.813]	1-66471-0
		3	3	49.89 [1.964]	29.74 [1.171]	66471-9
		3	1	37.97 [1.495]	17.81 [.701]	66471-7
		2	3	49.89 [1.964]	29.74 [1.171]	66471-3
		2	1	37.97 [1.495]	17.81 [.701]	66471-1
	POST FINISH	BODY FINISH	NO OF TERM	B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C.REIFSNYDER 07 JUN 96	TE Connectivity		
			CHK R.STONE 12 JUL 96			
			APVD G.A.STEINHAUER 23 JUL 96	NAME		
			PRODUCT SPEC	PIN CONTACT, CRIMPED, .062 DIA, .045 x .045 POST, -		
			APPLICATION SPEC			
			WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-66471
			CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV W