





- | | | |
|---|------------------|---|
|  | 0.38μm [.000015] | MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN. |
| | 1.27μm [.000050] | MIN TIN PER MIL-T-10727 FOR A LENGTH OF 5.69[.224] MIN ON OPPOSITE END, BOTH OVER |
| | 1.27μm [.000050] | MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT. |

- 17 SUPERCEDED BY 3-66104-2

16	OBSOLETE			BRASS	—	3-66104-3
	OBSOLETE			BRASS	—	3-66104-2
	OBSOLETE			BRASS	—	3-66104-1
14				BRASS	1-66105-9	3-66104-0
	STANDARD			BRASS	1-66105-9	2-66104-9
				BRASS	—	2-66104-7
	OBSOLETE			BRASS	1-66105-4	2-66104-6
				BRASS	—	2-66104-5
	OBSOLETE			PHOSPHOR BRONZE	1-66105-3	2-66104-3
	OBSOLETE			PHOSPHOR BRONZE	1-66105-2	2-66104-2
	OBSOLETE			BRASS	—	1-66104-9
	OBSOLETE			BRASS	—	1-66104-7
	OBSOLETE	STANDARD		BRASS	1-66105-0	1-66104-6
				BRASS	66105-4	66104-9
				BRASS	66105-3	66104-8
				BRASS	66105-2	66104-7
				BRASS	66105-1	66104-6
		STANDARD		BRASS	66105-4	66104-4
		STANDARD		BRASS	66105-3	66104-3
		STANDARD		BRASS	66105-2	66104-2
		STANDARD		BRASS	66105-1	66104-1
	REELING	BODY FINISH		BODY MATERIAL	LOOSE PIECE REF	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. FURLER 22JUL03		 TE Connectivity							
		CHK G. STEINHAUER 22JUL03									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET ASSEMBLY, .062 TYPE III+ —							
		APVD G. STEINHAUER 22JUL03									
		PRODUCT SPEC —									
		APPLICATION SPEC —									
		MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
SEE CALLOUTS		SEE CALLOUTS		WEIGHT	A2 00779		C-66104	—			
CUSTOMER DRAWING						SCALE	8:1	SHEET	1 of 1	REV	BR