




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT


REVISIONS				
P	F	ZONE	DESCRIPTION	DATE
✓	✓	F1	REVISED PER ECO-11-005294	05APR11
		F2	REV PER ECO 14-009346 CT	6-14

ASSIST SPRING
MATL: STAINLESS STEEL
PER QQ-S-766POINT OF PLATING
MEASUREMENTTERMINAL LATCH
MATL: NYLON
COLOR: (SEE TABLE)CONTACT BODY
MATL: COPPER PER QQ-C-576
FINISH: (SEE TABLE)AMP & WIRE SIZE STAMPED
ON INSULATION BARREL

SECTION B-B



SECTION C-C



SECTION A-A

① REELED FOR USE WITH STANDARD APPLICATORS.

② REELED FOR USE WITH HEAVY DUTY MINI-APPLICATORS.

③ PLATED WITH .000100 MIN SILVER PER QQ-S-365.

④ PLATED WITH .000015 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.

⑤ PLATED WITH .000030 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.

⑥ PLATED WITH .000050 MIN 93-7% TIN-LEAD ALLOY OVER .000030 MIN NICKEL PER QQ-N-290.

7. WIRE RANGE = 12-16 AWG.

8. INSULATION RANGE = .140-.165 DIA.

⑦ PLATED TIN (NO LEAD). 0.00050 MIN THK PER
ASTM-B-595 OVER NICKEL .000030 MIN THK PER QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±.010	CONTRACT NO		TE TE Connectivity	
	DR	9-25-85		
	CHK	8/8/85		
	APPD	8/8/85		
MATERIAL	SEE CALLOUT		NAME	
FINISH	SEE DASH NO		FEMALE TYPE XII CONTACT ASSEMBLY, WITH ASSIST SPRING	
OTHER APPD		DSGN APPD	SIZE	FSCM NO
			C	00779
			SCALE	DRAWING NO
			NTS	66740
				SHEET

BLACK	2-66740-1	2-66740-0/2	
BLACK	2-66740-1	1-66740-9/1	
BLACK	66740-8	1-66740-2/2	
BLACK	66740-6	1-66740-1/2	
BLACK	OBSOLETE	1-66740-0/2	
NATURAL	66740-2	66740-9/2	
BLACK	66740-8	66740-7/1	
BLACK	66740-6	66740-5/1	
BLACK	OBSOLETE	66740-3/1	
NATURAL	66740-2	66740-1/1	
TERMINAL LATCH COLOR	FINISH	LOOSE PIECE PART NO	STRIP PART NO

CUSTOMER DRAWING