



LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
G	86				
		3		REVISED PER ECO-13-018297	26NOV13
					DWN
					APVD
					CT



- 1 WIRE INSULATION: .520-.633 DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 FLASH PERMITTED $\pm .020$
- 4 STAMP "AMP 3/0 AL 13-78" SIZE AND LOCATION APPROX AS SHOWN SEE TABLE FOR QUALIFICATION PORTION OF STAMP U = UNQUALIFIED P = PRODUCTION (IMPACT PART)
- 5 PRELIMINARY - NOT FOR PRODUCTION



-	PRODUCTION AND QUALIFIED	P AMP	INSERT & FUNNEL: BRASS MIL-C-50 NICKEL PL QQ-N-290 .000300 AVG THK	5 696961-2
RED STRIPE	PRODUCTION AND UNQUALIFIED	P AMP U	BODY: COPPER ASTM-B187 ANNEALED TIN PL PER ASTM B-545 .000150 MIN THK	5 696961-1
COLOR CODE	QUALIFICATION DESCRIPTION 4	QUALIFICATION STAMP 4	MATERIAL & FINISH	PART NO.

1471-9 (3/11)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm -$

1 PLC $\pm -$

2 PLC $\pm -$

3 PLC $\pm .008$

4 PLC $\pm -$

ANGLES $\pm -$

FINISH

SEE TABLE

SEE TABLE

DWN JR RUTH 09MAY06

CHK MJ SPICER 09MAY06

APVD MJ SPICER 09MAY06

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 111 GRAMS

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 of 1

REV 3

TE Connectivity

WIRE TERMINAL, COPALUM

SEALED, RING TONGUE,

WIRE SIZE: 3/0 ALUMINUM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2 00779

C=696961

696961