





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T2	REVISED PER ECR-24-213591	28JUN2024	RK	FJS



- 1 1.27µm [.000050] MIN TIN-LEAD OVER
1.27µm [.000050] MIN NICKEL.
- 2 0.76µm [.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [.000010] ON REMAINDER, OVER 1.27µm [.000050] MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
- 3 0.76µm [.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27µm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA BOTH OVER 1.27µm [.000050] MIN NICKEL PLATE. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
- 4 0.38µm [.000015] MIN PRECIOUS METAL PLATE IN LOCALIZED PLATE AREA, 1.27µm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH ALL OVER 1.27µm [.000050] NICKEL. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).
- 5 WIRE RANGE 24-20 AWG.
- 6 INSULATION RANGE 2.03[.080]-2.54[.100] DIA.
- 7 0.38µm [.000015] MIN GOLD PER MIL-G-45204 ON LOCALIZED GOLD PLATE AREA, 1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
- 8 1.27µm [.000050] MIN TIN OVER
1.27µm [.000050] MIN NICKEL.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

	SMALL PACK	8	1-66332-4 OR 1-66332-5	1-66400-1
	STANDARD	8	1-66332-4 OR 1-66332-5	1-66400-0
	SMALL PACK	3	66332-4	66400-9
9 OBSOLETE	SMALL PACK	4	66332-3	66400-8
9 OBSOLETE	SMALL PACK	2	66332-6	66400-7
	SMALL PACK	1	66332-1	66400-6
OBSOLETE	STANDARD	7	1-66332-2	66400-5
	STANDARD	3	66332-4	66400-4
	STANDARD	4	66332-3	66400-3
	STANDARD	2	66332-6	66400-2
	STANDARD	1	66332-1	66400-1
	PACKAGING TYPE	FINISH	STRIP P/N REF	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 9-27-90	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK J.MCCLINTON 12-15-90			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD A.BOUILLIANNE 12-10-90		
	FINISH		PRODUCT SPEC		
MATERIAL		WEIGHT -	APPLICATION SPEC		
SEE CALL OUT		PIN BODY: SEE TABLE	-		
CUSTOMER DRAWING			SIZE A2	CAGE CODE 00779	DRAWING NO C-66400
			SCALE 8:1	SHEET 1 OF 1	REV T2