




CONTACT DIMENSIONS


RECOMMENDED PCB-HOLE LAYOUT
COMPONENT SIDE SHOWN

REFERENCE APPLICATION SPECIFICATION




	z	a	b	c	d	e	f
1	C	B	B	C	B	B	C
2	C	B	B	C	B	B	C
3	C	B	B	C	B	B	C
4	C	B	B	C	B	B	C
5	C	B	B	C	B	B	C
6	C	B	B	C	B	B	C
7	C	B	B	C	B	B	C
8	C	B	B	C	B	B	C
9	C	B	B	C	B	B	C
10	C	B	B	C	B	B	C
11	C	B	B	C	B	B	C
	MULTI PURPOSE CENTER						
15	C	B	B	C	B	B	C
16	C	B	B	C	B	B	C
17	C	B	B	C	B	B	C
18	C	B	B	C	B	B	C
19	C	B	B	C	B	B	C
20	C	B	B	C	B	B	C
21	C	B	B	C	B	B	C
22	C	B	B	C	B	B	C
23	C	B	B	C	B	B	C
24	C	B	B	C	B	B	C
25	C	B	B	C	B	B	C

  	1-6645436-9
  	6645436-9
 	6645436-4
 	6645436-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 190C1202 ORK: DAVID SHEN SANDERS YAN 190C1202		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: APVD: ALEX CAI 190C1202		NAME	
		PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029		MALE ASSEMBLY, Z-PACK 2mm HM, TYPE A	
MATERIAL		WEIGHT		SIZE A1	CAGE CODE 00779
 SEE TABLE		CUSTOMER DRAWING		DRAWING NO C-6645436	RESTRICTED TO -
				SCALE 4:1	SHEET 1 OF 2
				REV	A

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	OWN	APVD
			—	SEE SHEET 1	—	—	—

- 1
- MATERIAL:
CONTACT: COPPER ALLOY.
HOUSING: GLASS-FILLED POLYESTER.
- 2
- GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27μm MIN NICKEL AND ACTION
PIN: 0.5μm MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- 3
- CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.
- 4
- CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 1.
- 5
- CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
CENTRAL OFFICE APPLICATIONS.
- 6
- CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,
UNCONTROLLED ENVIROMENT APPLICATIONS.
- 7
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.
- 8
- PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
PATTERN DEFINED BY CONTACT LAYOUT.
- 9
- FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".
- 10
- FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".
- 11
- TO BE MEASURED AT BOTTOM OF SHROUD.
- 12
- POLARIZATION FEATURE.
- 13
- AREA RESERVED FOR KEYING PART (BASIC P/N 100525)
- 14
- CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID SHEN 19OCT2012		 TE Connectivity	
		CHK SANDERS YAN 19OCT2012			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0-PLC ±		APVD ALEX CAI 19OCT2012	
		1-PLC ± 0.1		PRODUCT SPEC	
		2-PLC ±		108-19082	
		3-PLC ±		APPLICATION SPEC	
4-PLC ±		ANGLES		SIZE	
FINISH		SEE SHEET 1		CAGE CODE	
MATERIAL SEE SHEET 1		WEIGHT —		DRAWING NO	
		CUSTOMER DRAWING		RESTRICTED TO	
		SCALE 4:1		SHEET 2 OF 2	
		REV A			