





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PROPOSAL DESIGN	21JUN2019	WY	SZ




POWER AND SIGNAL PINS

- 1 "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN. PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2 MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-O
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA OF POWER AND SIGNAL CONTACTS.
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7 PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.003 HOLE.

PROPOSAL ONLY

REVISIONS				
P	LTR	DESCRIPTION	DATE	OWN
-	-	SEE SHEET 1	-	-

PART NUMBER	ROWS		POWER				SIGNAL																					POWER								
			P8	P7	P6	P5	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	P4	P3	P2	P1			
7-6450860-9	D		GS	GS	GS	GS	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	GS	GS	GS	GS			
	C						AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP					AP	AP	AP
	B						AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP					AP	AP	AP
	A						AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP	AP					AP	AP	AP
4HDP+92S+4HDP																																				



STD PRESS FIT SIGNAL CONTACT, .135 TAIL LENGTH		AP
STD PRESS FIT POWER CONTACT, .135 TAIL LENGTH		GS
HOLD DOWN, MULTI-BEAM		HD
DESCRIPTION		IDENTIFIER
THIS DRAWING IS A CONTROLLED DOCUMENT.		NAME
DIMENSIONS: INCHES		SIZE
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CAGE CODE
MATERIAL		DRAWING NO
RESTRICTED CUSTOMER		REV