


*AMPPOWER is a trademark

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN
		C		REVISE PER 06-019-72 ECO	30/AUG/06	ECC
						APVD
						JS

1. CABLE LENGTH TOLERANCE ON 0-150 INCH LONG CABLES =
+0.2% -0% OF TOTAL CABLE LENGTH WITH A MINIMUM
TOLERANCE OF +6.4 [.25] -0.0 [.00].
- 2 26 AWG WIRE PER M22759/11 OR EQUIV.
- 3 TWISTED PAIRS AND TWISTED TRIPLES TO BE WRAPPED ABOUT
EACH OTHER AS SPECIFIED.
- 4 REFERENCE TEXAS INSTRUMENTS CRIMP TOOL #Z7054-00.
REFERENCE TEXAS INSTRUMENTS CRIMP TOOL POSITIONER #Z7054-01.

WIRE LIST		
CONNECTOR POSITION		COLOR
FROM	TO	
P1-17	P2-1	WHITE
P1-10	P2-13	BLUE
P1-16	P2-2	WHITE
P1-9	P2-14	BLUE
P1-3	P2-3	WHITE
P1-4	P2-15	BLUE
P1-15	P2-4	WHITE
P1-8	P2-16	BLUE
P1-1	P2-5	WHITE
P1-2	P2-17	BLUE
P1-11	P2-6	WHITE
P1-18	P2-18	BLUE
P1-7	P2-8	WHITE
P1-21	P2-20	BLUE
P1-14	P2-21	ORANGE
P1-13	P2-9	WHITE
P1-20	P2-10	BLUE
P1-6	P2-22	ORANGE
P1-19	P2-12	WHITE
P1-5	P2-23	BLUE
P1-12	P2-24	ORANGE

- TWISTED PAIR 4
- TWISTED PAIR 4
- TWISTED PAIR 4
- TWISTED PAIR 4
- TWISTED PAIR 4
- TWISTED PAIR 4
- TWISTED PAIR 4
- TWISTED PAIR 4
- TWISTED TRIPLE 4
- TWISTED TRIPLE 4
- TWISTED TRIPLE 4



235.0 [9.25]	766182-3
196.9 [7.75]	766182-2
158.8 [6.25]	766182-1
CABLE ASSY LENGTH A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	08AUG96	tyco Tyco Electronics Corporation Harrisburg, PA 17105-3608		
		CHK	12AUG96			
		APVD	12AUG96	NAME AMPPOWER* Wave Crimp System SIGNAL MODULE ASSY		
		PRODUCT SPEC				
		APPLICATION SPEC				
		114-49005		SIZE	CAGE CODE	DRAWING NO
		WEIGHT		A2	00779	C=766182
		CUSTOMER DRAWING		SCALE	N.T.S.	SHEET 1 of 1
				REV C		