






SECTION A-A



SECTION B-B

- 10 PRELIMINARY – NOT FOR PRODUCTION.

- △12 0.76μm [.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27μm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER .76μm [.000030] MIN NICKEL PER QQ-N-290. CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPEC 108-10042, BASED ON EIA-364-1000.01 (CONTROLLED ENVIRONMENT APPLICATIONS).

UNCONTROLLED - ENVIRONMENTAL DISPOSITION					
11	OBSOLETE	9	CU-NI ALLOY	-	10 1-66598-5
		8	BRASS	-	1-66598-4
		8	PHOSPHOR BRONZE	-	1-66598-3
		8	CU-NI ALLOY	1-66601-2	1-66598-2
		3	CU-NI ALLOY	1-66601-0	1-66598-1
		8	BRASS	-	1-66598-0
		8	BRASS	66601-9	66598-9
	OBSOLETE	7	BRASS	66601-5	66598-8
	OBSOLETE	2	BRASS	-	66598-7
11	SUPERSEDED	3	PHOSPHOR BRONZE	66601-4	66598-6
		2	PHOSPHOR BRONZE	66601-3	66598-5
		1	BRASS	-	66598-3
		12	BRASS	66601-2	66598-2
		2	BRASS	66601-1	66598-1
		BODY FINISH	BODY MATERIAL	LOOSE PIECE REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 8-11-88 CHK M.HOFFECKER J.McCLINTON 8-11-88		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME SOCKET ASSEMBLY, .062, TYPE III+	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE A2	CAGE CODE 00779
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		DRAWING NO C-66598	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 8:1	SHEET 1 OF 1
				REV AA	