


NUMBER 69154



"F" DIM.	
GO	NO GO
.144	.150

Gage dimensions apply when tool is bottomed but not under pressure.

FOR REPLACEMENT OF PARTS OTHER THAN LISTED, TOOL SHOULD BE RETURNED TO OUR FACTORY TO INSURE PROPER CERTI-CRIMP ADJUSTMENT.

INACTIVE
DATE 12-24-ECN D-3450

©1952 BY AMP INCORPORATED. ALL RIGHTS RESERVED.
AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

CUSTOMER COPY
REFERENCE ONLY

REQUIRED PER ASSEMBLY

LTR	REVISION RECORD	ECA	DATE	LTR	REVISION RECORD	ECA	DATE
5	REVISED		10-2-61				
4	REVISED		10-2-61				
3	REVISED		10-2-61				
2	REVISED		10-2-61				
1	REVISED		10-2-61				

1	A	21025-9	ROLL PIN	5
1	A	3-21001-1	SCREW	4
1	A	5-21010-0	SET SCREW	3
2	A	3-21001-8	SCREW	2
1	B	306199	FINGER GUARD	1

DWG NO	NUMBER	NAME	REMARKS	ITEM NO
69154				
WIRE RANGE		UNLESS OTHERWISE SPECIFIED: REMOVE BURRS, BREAK SHARP EDGES 1/64 R. MAX.		
AREA		OTHERWISE: FRACTIONS: ± 1/64 DECIMALS: .000 ± .005		
CLASS		SPECIFIED ANGLES: ± 0° 30'		
TYPE		F.C.B.M.P.		
DR	J. MOWER 9-25-61	FIRST USED		
CHK		P.P.P.		
APP		SCALE	NAME	
REL		1:1	HEAVY HEAD HAND TOOL ASSEMBLY	

AMP	AMP INCORPORATED HARRISBURG, PENNA.
NO 69154	REV E

DIMENSIONS IN INCHES. DO NOT SCALE. PRINT.