

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION ,19 .

© COPYRIGHT 19


BY AMP INCORPORATED. ALL RIGHTS RESERVED.

AMPOWER Is a registered trademark of AMP Incorporated.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		0	NEW RELEASE	08MAY03	ECC	JS

1. CABLE LENGTH TOLERANCE = 0.2% OF TOTAL CABLE LENGTH,
WITH A MINIMUM TOLERANCE OF ±3.18 [.125].
I.E. 6096 [240.0] * .002 = ± 12.2 [.480]

2 LABEL APPROX. WHERE SHOWN PER AMP 2480.0903.MPI.



151.26 [5.95]	7.92 [.312]	131.45 [5.175]	SOLID	0.25 [.010]	766608-1
C REF.	HOLE DIA. B	CABLE ASSEMBLY LENGTH A	STYLE	CONDUCTOR THICKNESS	PART #



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 07/MAY/03	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCH]		CHK J. SCHOLZ 08/MAY/03			
		APVD J. SCHOLZ 09/MAY/03	NAME AMPOWER WAVE CRIMP SYSTEM		
		PRODUCT SPEC -	CABLE ASSEMBLY		
MATERIAL -		APPLICATION SPEC 114-49005	SIZE A3	CAGE CODE 00779	DRAWING NO C- 766608
		FINISH -	WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING				SCALE FULL	SHEET 1 OF 1
				REV 0	