




LOC		DIST		REVISIONS				
P	LTN	DATE	DWN	APVD	DESCRIPTION			
A	DRAWN	18JUL2012	-	JE				




- △ REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- △ MATERIAL:
 CONTACT & SHIELD - PHOSPHOR BRONZE
 HOUSING & CHICKLET - GRAY GLASS FILLED POLYESTER
- △ FINISH: SIGNAL AND GROUND CONTACTS:
 MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
 COMPLIANT PIN AREA: 0.5 μm MIN MATTE TIN OVER BASE PLATING
- △ CONNECTOR MARKED WITH DATE CODE IN APPROXIMATE AREA SHOWN.
- △ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.

RECOMMENDED PC BOARD LAYOUT
 COMPONENT SIDE SHOWN
 SCALE 4:1



TOP SURFACE OF DAUGHTER CARD



6934117-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO 09JUN2006	TE Connectivity	
DIMENSIONS: mm		CHK R. PATTERSON 09JUN2006	NAME HEADER ASSEMBLY, RIGHT ANGLE, 4 PAIR, LATCHING, HMzd	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC #+ 1 PLC #+ 2 PLC #+ 3 PLC #+ 4 PLC #+ ANGLES #+ FINISH #+ #		APVD R. PATTERSON 09JUN2006	PRODUCT SPEC 108-2055	
MATERIAL △ 2		APPLICATION SPEC 114-13059	RESTRICTED TO	
		WEIGHT -	SIZE A100779C=6934117	
		CUSTOMER DRAWING	SCALE 6:1 SHEET 1 OF 1 REV A	