




LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REV PER ECO-10-011486			1JUNE2010	RG	MS

1. CABLE LENGTH TOLERANCE ON 0-150 INCH LONG CABLES = +0.2% -0% OF TOTAL CABLE LENGTH WITH A MINIMUM TOLERANCE OF +6.4 [.25] 0 [0].
CABLE LENGTH TOLERANCE ON CABLES OVER 150 INCHES LONG = + 1% -0% OF TOTAL CABLE LENGTH.

 LABEL APPROX. WHERE SHOWN PER AMP 2480.0903.MPI.



0.50 [.020]	SPLIT	182.88 [7.20]	234.74 [9.24]	766611-2
0.25 [.010]	SPLIT	339.3 [13.36]	391.16 [15.40]	766611-1
CONDUCTOR THICKNESS	STYLE	DIMENSION C	DIMENSION A	PART #
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIMENSIONS: mm [INCHES]  TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 [.02] 2 PLC ±0.25 [.010] 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		DWN E.C. CLAYBAUGH 07/MAY/03 CHK J. SCHOLZ 08/MAY/03 APVD J. SCHOLZ 12/MAY/03 PRODUCT SPEC - APPLICATION SPEC 114-49005 WEIGHT - CUSTOMER DRAWING	NAME AMPPOWER Wave Crimp System SIZE A2 CAGE CODE 00779 DRAWING NO C-766611	AMP Incorporated Harrisburg, PA 17105-3608 SCALE FULL SHEET 1 OF 1 REV B