



D



C

B

A



1. CABLE LENGTH TOLERANCE = 0.2% OF TOTAL CABLE LENGTH, WITH A MINIMUM TOLERANCE OF ± 6.4 [.252], I.E. $6096 [240.0] * .002 = \pm 12.2 [.480]$.
 2. 300V AC/DC CABLE ONLY.
 3. ALL ASSEMBLIES MADE WITH BLUE INSULATED CABLE.
 4. BECAUSE OF SHIPPING CONSTRAINTS, REFOLDING/SHAPING OF CABLE ASSEMBLIES MAY BE REQUIRED BY CUSTOMER BEFORE INSTALLATION.
- 5 LABEL APPROXIMATELY AS SHOWN.



1174.56 [46.242]	28 [1.102]	345 [13.583]	683 [26.890]	34 [1.339]	49 [1.929]	SPLIT	0.50 [.020]	766705-4
1157.56 [45.573]	28 [1.102]	267.5 [10.531]	730 [28.740]	47.5 [1.870]	49 [1.929]	SPLIT	0.50 [.020]	766705-3
1155.56 [45.494]	3 [.118]	319 [12.559]	693 [27.283]	81 [3.189]	24 [.945]	SPLIT	0.50 [.020]	766705-2
1156.06 [45.514]	3 [.118]	250 [9.842]	740 [29.134]	103.5 [4.075]	24 [.945]	SPLIT	0.50 [.020]	766705-1
TOTAL CABLE LENGTH	(E)	(D)	(C)	(B)	(A)	STYLE	(CONDUCTOR THICKNESS)	PART NUMBER

1	1	1	1	PC	3-1200603-7	POLY LABEL 1.88 X .69	5
SEE TABLE	IN	2-765210-0	CABLE .020 SPLIT				4
2	2	2	2	PC	765215-1	SEP TERMINATION ASSY	3
2	2	2	2	PC	765182-1	STRAIN RELIEF, FULL	2
2	2	2	2	PC	765181-1	HOUSING, PLUG	1
-4	-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.

DIMENSIONS: mm [INCHES]

MATERIAL

-

DWN

C. VALENTINE

11APR2012

CHK

D. ORRIS

11APR2012

APVD

D. ORRIS

11APR2012

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

NAME

CABLE ASSEMBLY, WAVE CRIMP

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A100779

766705

SCALE

NTS

SHEET

1

OF

1

REV

B