

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14	A	REV PER 0G3A-0193-05	31MAY05	JR TM

**AMP**  
WIRE RANGE

---

16-14 HD  
STRANDED

- 1 WIRE INSULATION DIA .105 TO .170
- 2 COPPER PER ASTM B-152  
NYLON, YELLOW
- 3 TIN PLATE PER ASTM B-545
- 4 PRELIMINARY - NOT FOR PRODUCTION
- 5 PARTS MANUFACTURED AFTER MAY 2005 ARE  
ROHS COMPLIANT.



50	LOOSE PIECE	4	696486-1
QTY	PACKAGE TYPE	PART NO	

<b>AMP INCORPORATED CUSTOMER SERVICE SYSTEMS</b>		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 16JAN03	<b>tyco</b> <b>Electronics</b>	Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300V MAX	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK T MICHIELUTTI 16JAN03		NAME SPLICE, BUTT, PIDG WIRE SIZE: 16-14 AWG					
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± .008 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD T MICHIELUTTI 16JAN03	PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	MATERIAL COPPER 2	FINISH TIN PLATE 3	—	APPLICATION SPEC	—	—	—	—		
					WEIGHT		A300779		C-696486			
					CUSTOMER DRAWING		SCALE	1:1	SHEET	1 OF 1	REV	A