

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECR-24-226486	20NOV2024	TB	JP



1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.

2 0.00381 MIN MATTE TIN LEAD PLATE OVER 0.00127 MIN NICKEL.

3 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

4 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.

5 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



RECOMMENDED LAYOUT FOR 1.57 THICK BOARD
TOLERANCES NON-ACCUMULATIVE

	BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-770166-1
	BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-770166-0
SUPERSEDED WITH 1-770166-1	-BRASS, GOLD	3	NYLON, UL94V-0	WHITE	770166-2
SUPERSEDED WITH 1-770166-0	BRASS, TIN-LEAD	2	NYLON, UL94V-0	WHITE	770166-1
	MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER 08JUN05	TE Connectivity		
DIMENSIONS: INCHES	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	CHK R JONES 28JUL2003			
	0 PLC ± -	APVD R JONES 28JUL2003	NAME		
	1 PLC ± -	PRODUCT SPEC	HEADER ASSEMBLY, 2 CKT, MINI UNIVERSAL MATE-N-LOK		
MATERIAL	2 PLC ± 0.13	APPLICATION SPEC	-		
	3 PLC ± -	WEIGHT	SIZE	CAGE CODE	DRAWING NO
	4 PLC ± -	CUSTOMER DRAWING	A2	00779	C-770166
	ANGLES ± -		SCALE	SHEET	REV
	FINISH		5:1	1 OF 1	N