




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECR-24-226486	20NOV2024	TB	JP




- 1 PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 2 0.00381 MIN MATTE TIN LEAD PLATE OVER 0.00127 MIN NICKEL.
- 3 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 4 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.
- 5 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



RECOMMENDED LAYOUT FOR 1.57 THICK BOARD
TOLERANCES NON-ACCUMULATIVE

	BRASS, TIN	4	NYLON, UL94V-0	BLACK	5-770174-0
	BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-770174-1
	BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-770174-0
SUPERSEDE WITH 1-770174-1	BRASS, GOLD	3	NYLON, UL94V-0	WHITE	770174-2
SUPERSEDE WITH 1-770174-0	BRASS, TIN-LEAD	2	NYLON, UL94V-0	WHITE	770174-1
	MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER 08JUN05		 TE Connectivity				
		CHK R JONES 28/JUL2003						
DIMENSIONS: mm		APVD R JONES 28JUL2003		NAME HEADER ASSEMBLY, 4 CKT, MINI UNIVERSAL MATE-N-LOK —				
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C-770174	RESTRICTED TO —	
		CUSTOMER DRAWING				SCALE 5:1	SHEET 1 of 1	REV N