





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECR-24-226486	20NOV2024	TB	JP

- PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- DIMENSIONS SHOWN IN BRACKETS ARE IN INCHES.

- △3 0.00076 [.000030] MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 [.000150] MATTE TIN LEAD IN THE LOCALIZED TIN LEAD PLATE AREA, BOTH OVER 0.00127 [.000050] MIN NICKEL.
- △4 0.00381 [.000150] MATTE TIN LEAD OVER 0.00127 [.000050] MIN NICKEL ENTIRE LENGTH OF PIN.
- △5 0.00381 [.000150] MATTE TIN OVER 0.00127 [.000050] MIN NICKEL ENTIRE LENGTH OF PIN.
- △6 0.00076 [.000030] MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 [.000150] MATTE TIN IN THE LOCALIZED TIN PLATE AREA, BOTH OVER 0.00127 [.000050] MIN NICKEL.



RECOMMENDED LAYOUT FOR 1.57[.062] THICK BOARD
TOLERANCES NON-ACCUMULATIVE



BRASS	△6	NYLON, UL94V-0	WHITE	1-770876-1
BRASS	△5	NYLON, UL94V-0	WHITE	1-770876-0
SUPERSEDED WITH 1-770876-1	△3	NYLON, UL94V-0	WHITE	770876-2
SUPERSEDED WITH 1-770876-0	△4	NYLON, UL94V-0	WHITE	770876-1
MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER 09JUN05	TE Connectivity	
DIMENSIONS: mm		CHK R JONES 29JUL2003		
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD R JONES 29JUL2003	NAME	
0 PLC ± -		PRODUCT SPEC	HEADER ASSEMBLY CLOSED BOTTOM, 9 CKT, MINI UNIVERSAL MATE-N-LOK	
1 PLC ± -		APPLICATION SPEC		
2 PLC ± 0.13		—	SIZE	CAGE CODE
3 PLC ± -		—	A2	00779
4 PLC ± -		WEIGHT	—	DRAWING NO
ANGLES ± -		CUSTOMER DRAWING	SCALE	5:1
FINISH		—	SHEET	1 OF 1
—		—	REV	H