



REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	CREATION	11FEB2020	JB	GN

NUMBER OF CRIMPS: 2X2 (width=9mm) or 2x3 (width=5mm)



CONDUCTORS						PART NUMBER	REFERENCE	Ø A	Ø B	PACKAGING
Cond. A			Cond. B							
Material	Section mm ²	Shape	Material	Section mm ²	Shape					
Alu	10	Stranded	Alu	25	Solid	709143-2	MJPBAS 10-25M	4.3	5.9	10
Alu	10	Stranded	Alu	35	Solid	709143-3	MJPBAS 10-35M	4.3	6.9	10
Alu	16	Stranded	Alu	10	Solid	709143-4	MJPBAS 16-10M	5.3	3.8	10
Alu	16	Stranded	Alu	16	Solid	709143-5	MJPBAS 16-16M	5.3	4.8	10
Alu	16	Stranded	Alu	25	Solid	709143-6	MJPBAS 16-25M	5.3	5.9	10
Alu	16	Stranded	Alu	35	Solid	709143-7	MJPBAS 16-35M	5.3	6.9	10
Alu	25	Stranded	Alu	16	Solid	709143-8	MJPBAS 25-16M	6.5	4.8	10
Alu	25	Stranded	Alu	25	Solid	709143-9	MJPBAS 25-25M	6.5	5.9	10
Alu	25	Stranded	Alu	35	Solid	1-709143-0	MJPBAS 25-35M	6.5	6.9	10
Alu	35	Stranded	Alu	35	Solid	1-709143-1	MJPBAS 35-35M	6.9	6.9	10
Alu	10	Stranded	Alu	10	Solid	1-709143-3	MJPBAS 10-10M	4.3	3.8	10
Alu	10	Stranded	Alu	06	Solid	1-709143-4	MJPBAS 10-06M	4.3	3.0	10
Alu	25	Stranded	Alu	10	Solid	1-709143-5	MJPBAS 25-10M	6.5	3.8	10
Alu	25	Stranded	Copper	21	Stranded	1-709143-6	MJPBAS 25-21CU	6.5	6.9	10
Alu	16	Stranded	Copper	21	Stranded	1-709143-7	MJPBAS 16-21CU	5.3	6.9	10
Alu	16	Stranded	Alu	6	Solid	1-709143-8	MJPBAS 16-6M	5.3	3.0	8x10
Alu	25	Stranded	Alu	10	Solid	1-709143-9	MJPBAS 25-10M	6.5	3.8	5x10
Alu	16	Stranded	Alu	4	Solid	2-709143-0	MJPBAS	TOLERANCES UNLESS OTHERWISE SPECIFIED: -	2.7	5x10

RING COLOR CODE:
 4: IVORY
 6: BROWN
 10: GREEN
 16: BLUE
 21: RED
 25: ORANGE
 35: RED

MARKING:
 - ACCORDING TO CROSS SECTION
 - DIE: E140
 - REFERENCE

THIS DRAWING IS A CONTROLLED DOCUMENT.
 CE PLAN EST UN DOCUMENT CONTROLE PAR TYCO ELECTRONICS CORPORATION
 IL EST SUSCEPTIBLE D'ETRE REVISE. POUR OBTENIR LA DERNIERE REVISION,
 CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS SIMEL SAS,
 21220 GEVREY-CHAMBERTIN, FRANCE.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES): 0 PLC/DEC: ±0 1 PLC/DEC: ±0 2 PLC/DEC: ±0 3 PLC/DEC: ±0 4 PLC/DEC: ±0 ANGLES ±
MATERIAL MATIERE	FINISH FINITION

DWN/DESSINE J. BERLAND 11/02/20	CHK/VERIFIE B. MILLOT	APVD/APPROUVE G. NEDELLEC
PRODUCT SPEC SPEC. PRODUIT	APPLICATION SPEC SPEC. APPLICATION	WEIGHT MASSE APPROX.
CUSTOMER DRAWING /PLAN CLIENT		

TE TE Connectivity

NAME TITRE: MJPBAS ---

SIZE FORMAT: A3

CAGE CODE: -

DRAWING NO No PLAN: C-709143

RESTRICTED TO RESERVE A

UNIQUEMENT POUR REFERENCE

SCALE ECHELLE: 1:1

SHEET FEUILLE: | OF DE: |

REV: A