



2 LABEL APPROX. WHERE SHOWN PER AMP 2480.0903.MPI.



0.25 [0.010]		SOLID	352.04 [13.86]		403.86 [15.90]		766612-1	
CONDUCTOR THICKNESS		STYLE	DIMENSION C		DIMENSION A		PART #	
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			DWN E.C. CLAYBAUGH 07/MAY/03		 AMP Incorporated Harrisburg, PA 17105-3608			
			CHK J. SCHOLZ 08/MAY/03					
DIMENSIONS: min [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. SCHOLZ 12/MAY/03		NAME AMPOWER Wave Crimp System		
		0 PLC ±-		PRODUCT SPEC - APPLICATION SPEC 114-49005		CABLE ASSY		
		1 PLC ±0.5 [0.02] 2 PLC ±0.25 [0.010] 3 PLC ±- 4 PLC ±- ANGLES ±-						
MATERIAL -		FINISH -		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-766612
CUSTOMER DRAWING						SCALE FULL	SHEET 1 OF 1	REV A