





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECR-24-226486	20NOV2024	TB	JP



RECOMMENDED HOLE PATTERN FOR 1.57 THICK BOARD



1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 2

0.00381 MIN MATTE TIN LEAD OVER 0.00127 MIN NICKEL.
- 3

0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 4

0.00381 MIN MATTE TIN OVER 0.00127 MIN NICKEL.
- 5

0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-770621-1
BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-770621-0
SUPERSEDED WITH 1-770621-1 BRASS, GOLD	3	NYLON, UL94V-0	WHITE	770621-2
SUPERSEDED WITH 1-770621-0 BRASS, TIN-LEAD	2	NYLON, UL94V-0	WHITE	770621-1
MATERIAL	FINISH	MATERIAL	COLOR	PART NO.
PIN		HOUSING		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER 08JUN05	TE Connectivity		
DIMENSIONS: mm		CHK R JONES 12AUG2003			
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APVD R JONES 12AUG2003	NAME		
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC	HEADER ASSEMBLY, CLOSED BOTTOM, 12 CKT, DOUBLE ROW VERTICAL, MINI UNIVERSAL MATE-N-LOK		
MATERIAL	FINISH	APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C-770621
-	-	WEIGHT -	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV N