

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECR-24-226486	20NOV2024	TB	JP

1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
2. DIMENSIONS SHOWN IN BRACKETS ARE IN INCHES.




- 3

0.00076 [.000030] MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 [.000150] MATTE TIN LEAD IN THE LOCALIZED TIN LEAD PLATE AREA, BOTH OVER 0.00127 [.000050] MIN NICKEL.
- 4


0.00381 [.000150] MATTE TIN LEAD OVER 0.00127 [.000050] MIN NICKEL ENTIRE LENGTH OF PIN.
- 5

0.00381 [.000150] MATTE TIN OVER 0.00127 [.000050] MIN NICKEL ENTIRE LENGTH OF PIN.
- 6


0.00076 [.000030] MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 [.000150] MATTE TIN IN THE LOCALIZED TIN PLATE AREA, BOTH OVER 0.00127 [.000050] MIN NICKEL.



RECOMMENDED LAYOUT FOR 1.57 [.062] THICK BOARD
TOLERANCES NON-ACCUMULATIVE



	BRASS	6	NYLON, UL94V-0	WHITE	1-770873-1
	BRASS	5	NYLON, UL94V-0	WHITE	1-770873-0
SUPERSEDED WITH 1-770873-1	BRASS	3	NYLON, UL94V-0	WHITE	770873-2
SUPERSEDED WITH 1-770873-0	BRASS	4	NYLON, UL94V-0	WHITE	770873-1
	MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER 08JUN05		 TE Connectivity							
		CHK R JONES 29JUL2003									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R JONES 29JUL2003		NAME					
		0 PLC ± -		PRODUCT SPEC		HEADER ASSEMBLY CLOSED BOTTOM, 3 CKT, MINI UNIVERSAL MATE-N-LOK					
		1 PLC ± -		—							
		2 PLC ± 0.13		APPLICATION SPEC							
		3 PLC ± -		—							
4 PLC ± -		ANGLES ± -		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL —		FINISH —		WEIGHT —		A2	00779	C-770873	—		
CUSTOMER DRAWING						SCALE	5:1	SHEET	1 of 1	REV	H