

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A12	REVISED PER ECO-21-001365	26JAN2021	DS	DS
	A13	REVISED PER ECR-24-216938	13SEP2024	DK	CB
	B	ECR-25-236813	23JUN2025	DK	EC

⚠ SUGGESTED MOUNTING SCREW SIZE IS Ø2.50mm [APPROX. 0.099 INCH] SELF TAPPING THREAD FORMING SCREW, SUCH AS DELTA PT, TO BE DRIVEN AT 0.6-0.8 N-m. THE CUSTOMER MUST TEST THE SCREW SIZE AND TYPE IN ORDER TO VERIFY THEIR SELECTION BEFORE USE IN APPLICATION

TO VALIDATE HEADER MOUNTING PERFORMANCE, TE CONNECTIVITY WILL CONTINUE TO UTILIZE THE FOLLOWING TORQUE VALIDATION PROCESS ACCORDING TO APPLICATION SPEC 114-16016:
MOUNTING PANEL THICKNESS - 4.75 +/- 0.15mm
SCREW - 2.5X12mm DELTA PT



CUSTOMERS MAY VALIDATE OTHER SCREW SIZES AND TYPES AT THEIR OWN DISCRETION

⚠ DATE CODE IN THIS LOCATION USING 5 DIGIT CODE
FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK
LAST DIGIT = DAY


⚠ MATERIALS: HEADER HOUSING - GLASS FILLED PBT
PINS - TIN OR GOLD PLATED BRASS
GASKET - SILICONE

⚠ HOUSING COLORS ARE MECHANICALLY KEYED TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.

5. HEADER MATES TO PLUG ASSEMBLY 776273 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854









SECTION A-A





776262-1 & 1-776262-1 SHOWN

BLUE	GOLD	1-776262-5
GRAY	GOLD	1-776262-4
NATURAL	GOLD	1-776262-2
BLACK	GOLD	1-776262-1
BLUE	TIN	776262-5
GRAY	TIN	776262-4
NATURAL	TIN	776262-2
BLACK	TIN	776262-1
HEADER COLOR	PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	03MAR2010	<div><div>TE</div><div>TE Connectivity</div><div>ASSEMBLY, HEADER, 14 POSITION, VERTICAL, AMPSEAL WITH FLANGE SEAL</div></div>									
DIMENSIONS:			CHK	22MAR2010										
mm			APVD	27APR2010										
TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC											
			0 PLC ±0.2	108-1329	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
			1 PLC ±0.2	APPLICATION SPEC										
			2 PLC ±0.2	114-16016	A1	00779	C=776262	-						
			3 PLC ±0.2	WEIGHT					17.10g					
			4 PLC ±0.2		CUSTOMER DRAWING		SCALE	4:1	SHEET	1	OF	2	REV	B
MATERIAL			ANGLES ±0.2											
			FINISH											
														



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03MAR2010 CHK D. STRAUSSER D. STRAUSSER APP'D 27APR2010 D. STRAUSSER		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.2 2 PLC ±. 3 PLC ±. 4 PLC ±. FINISH ANGLES ±.		NAME ASSEMBLY, HEADER, 14 POSITION, VERTICAL, AMPSEAL WITH FLANGE SEAL	
		PRODUCT SPEC 108-1329 APPLICATION SPEC 114-16016		SIZE CAGE CODE DRAWING NO	
MATERIAL - -		WEIGHT 17.10g		RESTRICTED TO - -	
CUSTOMER DRAWING		SCALE 2:1		SHEET 2 OF 2 REV B	