





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECO-12-021105	28DEC2012	CJV	SLB



- 1 0.76µm [.000030] MIN GOLD ON LOCALIZED GOLD PLATE AREA, 2.54 [.000100] MIN TIN-LEAD ON LOCALIZED TIN PLATE AREA, ALL OVER 1.27µm [.000050] MIN NICKEL.
- 2 GOLD FLASH ON LOCALIZED GOLD PLATE AREA, 2.54µm [.000100] MIN TIN-LEAD ON LOCALIZED TIN PLATE AREA, ALL OVER 1.27µm [.000050] MIN NICKEL.
- 4 0.76µm [.000030] MIN GOLD ON LOCALIZED GOLD PLATE AREA, 2.54 [.000100] MIN TIN ON LOCALIZED TIN PLATE AREA, ALL OVER 1.27µm [.000050] MIN NICKEL.
- 5 GOLD FLASH ON LOCALIZED GOLD PLATE AREA, 2.54µm [.000100] MIN TIN ON LOCALIZED TIN PLATE AREA, ALL OVER 1.27µm [.000050] MIN NICKEL.



	-	7.39 [.291]	20.65 [.813]	5	1-788063-5
	-	18.80 [.740]	32.05 [1.262]	5	1-788063-4
	-	13.16 [.518]	26.42 [1.040]	4	1-788063-3
OBSOLETE	PER DETAIL H	7.39 [.291]	20.65 [.813]	5	1-788063-2
	PER DETAIL H	18.80 [.740]	32.05 [1.262]	5	1-788063-1
	PER DETAIL H	13.16 [.518]	26.42 [1.040]	4	1-788063-0
	PER DETAIL H	18.80 [.740]	32.05 [1.262]	2	788063-6
	-	18.80 [.740]	32.05 [1.262]	2	788063-5
	PER DETAIL H	13.16 [.518]	26.42 [1.040]	1	788063-3
	-	13.16 [.518]	26.42 [1.040]	1	788063-2
	LOOSE PIECE	B	A	FINISH	PART NUMBER



DETAIL H

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009				DWN C.OBERMAN 16 SEP 96	TE Connectivity		
DIMENSIONS: INCHES				CHK R.STONE 17 SEP 96			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD K.DOWHOWER 18 SEP 96	NAME		
0 PLC ± -				PRODUCT SPEC	SOCKET CONTACT, SIZE 20 DF, AMPLIMITE		
1 PLC ± -				APPLICATION SPEC			
2 PLC ± 0.13 [.005]				108-40005	SIZE		
3 PLC ± -				114-10000	CAGE CODE		
4 PLC ± -				WEIGHT	DRAWING NO		
ANGLES ± -				CUSTOMER DRAWING	RESTRICTED TO		
FINISH				SCALE	SHEET		
SEE TABLE				10:1	1 of 1		
PHOSPHOR BRONZE				REV	B		