

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E2	REVISED PER ECR-23-188565	18SEP2024	TB	JP

D

C

B


A

D



C

B


A



1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.5 – 0.15mm² (30–26 AWG). mm
3. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SECTION A—A
SCALE 20:1



SECTION B—B
SCALE 20:1

SUPERSEDED WITH 1-794059-0

3	0.20 [.008] BRASS	1-794059-0
1	0.20 [.008] BRASS	794059-3
PRE-TIN	0.20 [.008] BRASS	794059-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 05MAR03	 TE Connectivity									
		CHK C. JONES 05MAR03										
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. JONES 05MAR03	NAME PIN, LOOSE PIECE MINI UNIVERSAL MATE-N-LOK(TM)		SIZE A2		CAGE CODE 00779		DRAWING NO C-794059		RESTRICTED TO —	
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.13[.005] 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC —										
		APPLICATION SPEC —										
MATERIAL —	FINISH —	WEIGHT —										
CUSTOMER DRAWING							SCALE 10:1	SHEET 1 of 1	REV E2			

METRIC