






REVISIONS					
REV	DATE	DESCRIPTION	BY	CHK	APP'D
F	20NOV2024	REVISED PER ECR-24-226486	TB	JP	



RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57 THICK P.C. BOARD

- PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 0.00381 MIN MATTE TIN LEAD PLATE OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

SUPERSEDED WITH 1-794065-1
 SUPERSEDED WITH 1-794065-0

MATERIAL	FINISH	MATERIAL	COLOR	PART NO.
BRASS, TIN	4	HIGH TEMP NYLON, UL94V-2	BLACK	6-794065-0
BRASS, TIN	4	HIGH TEMP NYLON, UL94V-0	BLACK	5-794065-0
BRASS, GOLD	5	NYLON, UL94V-0	WHITE	1-794065-1
BRASS, TIN	4	NYLON, UL94V-0	WHITE	1-794065-0
BRASS, GOLD	3	NYLON, UL94V-0	WHITE	794065-2
BRASS, TIN-LEAD	2	NYLON, UL94V-0	WHITE	794065-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN S CARPENTER 09JUN05		TE Connectivity	
DIMENSIONS: mm		CHK R JONES 28JUL2003		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D R JONES 28JUL2003		PRODUCT SPEC	
0. PLC ± -		APPLICATION SPEC		SIZE	
1. PLC ± -		WEIGHT		CAGE CODE	
2. PLC ± 0.13		A1 00779		DRAWING NO	
3. PLC ± -		CUSTOMER DRAWING		RESTRICTED TO	
4. PLC ± -		SCALE 8:1		SHEET 1 of 1	
ANGLES ± -		REV F			