






1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 108-11-3.
- 0.00381 MIN MATTE TIN LEAD OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- 0.00381 MIN MATTE TIN OVER 0.00127 MIN NICKEL.
- 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



	BRASS, GOLD	5	NYLON, 94V-0, WHITE	1-794079-1
	BRASS, TIN	4	NYLON, 94V-0, WHITE	1-794079-0
OBSOLETE	BRASS, GOLD	3	NYLON, 94V-0, WHITE	-794079-2-
OBSOLETE	BRASS, TIN LEAD	2	NYLON, 94V-0, WHITE	-794079-1-
PIN CONTACT MATERIAL AND FINISH			HOUSING MATERIAL AND COLOR	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN K. WHITAKER 6-12-95 CHK R. SWING 6-12-95 APVD R. ORSTAD 6-13-95 NAME	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC
mm		0. PLC ± -		APPLICATION SPEC
		1. PLC ± -		
		2. PLC ± 0.13		
		3. PLC ± -		
		4. PLC ± -		
		ANGLES ± -		
MATERIAL	SEE TABLE	FINISH	SEE TABLE	WEIGHT
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1