





	57.91 [2.280]	63.88 [2.515]	46.13 [1.816]	57.91 [2.280]	68	787927-7
OBSOLETE	40.13 [1.580]	46.10 [1.815]	28.35 [1.116]	40.13 [1.580]	40	787927-4
	L	D	B	A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG 17 JAN 97 C.DORWART 05 FEB 97 R.WALTER 05 FEB 97		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm[INCHES] 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± . 2 PLC ± .13 [.005] 3 PLC ± . 4 PLC ± . ANGLES ± .		NAME RECEPTACLE ASSEMBLY, SHIELDED, RIGHT ANGLE, .050 SERIES AMPLIMITE PRODUCT SPEC 108-1228 APPLICATION SPEC 114-40029	
MATERIAL 		FINISH 		SIZE CASE CODE DRAWING NO RESTRICTED TO: TO A1 00779 C=787927 —	
CUSTOMER DRAWING		WEIGHT —		SCALE 4:1 SHEET 1 OF 1 REV K	