

D

B

C




C

B

B

A

A



1.00	.039	6.10	.240	—	—
0.76	.030	5.99	.236	42.98	1.692
0.25	.010	5.33	.210	18.631	.7335
0.13	.005	5.08	.200	14.491	.5705
0.08	.003	4.14	.163	12.70	.500
0.064	.0025	3.86	.152	10.351	.4075
0.05	.002	3.68	.145	9.80	.386
0.00381	.000150	2.070	.0815	7.34	.289
0.00127	.000050	1.57	.062	6.86	.270
0.00076	.000030	1.40	.055	6.210	.2445
MM	IN	MM	IN	MM	IN
CONVERSION TABLE					

RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 THICK P.C. BOARD

OBSOLETE	BRASS	GOLD 8	NYLON, UL94V-0	WHITE	1-794106-1
	BRASS	TIN 7	NYLON, UL94V-0	WHITE	1-794106-0
	BRASS	GOLD 6	NYLON, UL94V-0	WHITE	794106-2
	BRASS	TIN LEAD 5	NYLON, UL94V-0	WHITE	794106-1
MATERIAL		FINISH	MATERIAL	COLOR	PART NO
PIN			HOUSING		
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN K. WHITAKER CHK R. SWING APVD R. ORSTAD	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC	± .	PRODUCT SPEC	
		1 PLC	± .	APPLICATION SPEC	
		2 PLC	± 0.13		
		3 PLC	± .		
MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT —	RESTRICTED TO	
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV D