





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECR-23-188565	18SEP2024	TB	JP




1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.12 – 0.4mm² (26–22 AWG).
3. INSULATION RANGE :1.20–1.75[.047–.069] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



METRIC

OBSOLETE	5	0.20 [.008] BRASS	1-794136-0
	1	0.20 [.008] BRASS	794136-3
	PRE-TIN	0.20 [.008] BRASS	794136-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 22OCT96		 TE Connectivity							
		CHK R. SWING 22OCT96									
		APVD R. ORSTAD 22OCT96									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		0 PLC ± -		SOCKET, MINI UNIVERSAL MATE-N-LOK(TM)							
		1 PLC ± -									
		2 PLC ± -									
		3 PLC ± 0.15[.006]									
		4 PLC ± -									
MATERIAL		ANGLES ± 1°		APPLICATION SPEC							
SEE TABLE		FINISH		RESTRICTED TO							
				SIZE		CAGE CODE		DRAWING NO		—	
				A2		00779		C=794136			
				CUSTOMER DRAWING		SCALE		10:1		SHEET 1 of 1	
										REV B1	