

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	REVISED PER ECR-23-188565	18SEP2024	TB	JP

- 1




0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
- 2

WIRE RANGE: 0.05 – 0.15MM² (30-26 AWG).
- 3

INSULATION RANGE: 0.89-1.27[.035-.050] DIA.
- 4


DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SUPERSEDED WITH 1-794216-0

5	0.25[.010] BRASS	1-794216-0
1	0.25[.010] BRASS	794216-3
PRE-TIN	0.25[.010] BRASS	794216-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97		 TE Connectivity							
DIMENSIONS: mm [INCHES]		CHK R. SWING 1-15-97									
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.15 [.006] 4 PLC ± - ANGLES ± -		PIN, MINI UNIVERSAL MATE-N-LOK 2 -							
		APVD -		PRODUCT SPEC -		APPLICATION SPEC -		RESTRICTED TO -			
		MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A2		CAGE CODE 00779		DRAWING NO C=794216	
		WEIGHT -		SCALE 10:1				SHEET 1 of 1		REV D3	
		CUSTOMER DRAWING									