




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECR-24-226486	20NOV2024	TB	JP




- PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.
- 0.00076 [.000030] MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 [.000150] MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 [.000050] MIN NICKEL.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- 0.00381 [.000150] MATTE TIN LEAD OVER 0.00127 [.000050] MIN NICKEL ENTIRE LENGTH OF PIN.
- 0.00076 [.000030] MIN GOLD PLATE IN THE LOCALIZED GOLD PLATE AREA, 0.00381 [.000150] MATTE TIN IN THE LOCALIZED TIN PLATE AREA, BOTH OVER 0.00127 [.000050] MIN NICKEL.
- 0.00381 [.000150] MATTE TIN OVER 0.00127 [.000050] MIN NICKEL ENTIRE LENGTH OF PIN.



RECOMMENDED LAYOUT FOR 1.57 [.062] THICK BOARD
TOLERANCES NON-ACCUMULATIVE



SUPERSEDE WITH 1-794040-1	BRASS, GOLD	5	NYLON, 94V-O, WHITE	1-794040-1
	BRASS, TIN	6	NYLON, 94V-O, WHITE	1-794040-0
	BRASS, GOLD	2	NYLON, 94V-O, WHITE	1-794040-2
	BRASS, TIN	4	NYLON, 94V-O, WHITE	794040-1
PIN CONTACT MATERIAL AND FINISH			HOUSING MATERIAL AND COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 2-8-94	 TE Connectivity				
		CHK R. SWING 2-8-94					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	NAME HEADER ASSEMBLY, CLOSED BOTTOM, 12 CIRCUIT, MINI-UNIVERSAL MATE-N-LOK				
		PRODUCT SPEC —					
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 3 PLC ± — 4 PLC ± — ANGLES ± —	APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C-794040	RESTRICTED TO —	
		WEIGHT —					
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV E