

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REDRAWN PER ECR-17-012999	14NOV2018	BDA	SG
	H1	REVISED PER ECR-20-100491	07OCT2020	PC	SW
	H3	REVISED PER ECR-23-188565	04NOV2024	BN	JP






1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.

2 WIRE RANGE: 0.05-0.15MM² (30-26 AWG).

3 INSULATION RANGE: 0.89-1.27[.035-.050] DIA.

4 DIMENSIONS IN BRACKETS ARE IN INCHES.

5 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.



SUPERSEDED WITH 1-794217-0	5	0.25[.010] BRASS	1-794217-0
	4	0.25[.010] BRASS	794217-3
	PRE TIN	0.25[.010] BRASS	794217-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK R. SWING 1-15-97		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. SWING -	NAME SOCKET, MINI UNIVERSAL MATE-N-LOK™2	
		PRODUCT SPEC -		
		APPLICATION SPEC -		
MATERIAL SEE TABLE -	SEE TABLE -	WEIGHT -	SIZE A1 CAGE CODE 00779 ©=794217	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1 REV H3