




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REVISED PER ECR-24-226486	20NOV2024	TB	JP

1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.

0.00381 MIN MATTE TIN LEAD PLATE OVER 0.00127 MIN NICKEL.

0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

0.00381 MIN MATTE TIN PLATE OVER 0.00127 MIN NICKEL.

0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.

RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57 THICK P.C. BOARD

	BRASS, GOLD	NYLON, 94V-0, WHITE	1-794073-1
	BRASS, TIN	NYLON, 94V-0, WHITE	1-794073-0
SUPERSEDE WITH 1-794073-1	BRASS, GOLD	NYLON, 94V-0, WHITE	1-794073-2
SUPERSEDE WITH 1-794073-0	BRASS, TIN LEAD	NYLON, 94V-0, WHITE	1-794073-1
PIN CONTACT MATERIAL AND FINISH		HOUSING MATERIAL AND COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER CHK R. SWING APVD R. ORSTAD PRODUCT SPEC	6-12-95 6-12-95 6-13-95	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0. PLC ± - 1. PLC ± - 2. PLC ± 0.13 3. PLC ± - 4. PLC ± - ANGLES ± - FINISH SEE TABLE		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
MATERIAL SEE TABLE		WEIGHT -		A100779C794073	
CUSTOMER DRAWING		SCALE 8:1		SHEET 1 OF 1 REV E	