

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECR-17-013000	30OCT2018	BD A	SG
	J2	REVISED PER ECR-23-188565	04NOV2024	BN	JP






1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254-0.00635 [.000100-.000250] BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.

2 WIRE RANGE: 0.5-1.4MM² (20-16 AWG).

3 INSULATION RANGE: 2.01-3.20[.079-.126] DIA.

4 DIMENSIONS IN BRACKETS ARE IN INCHES.

5 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254-0.00635 [.000100-.000250] BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.



SUPERSEDED WITH 1-794223-0

5	MAKE FROM 794223-2	1-794223-0
1	MAKE FROM 794223-2	794223-3
PRE TIN	.0098±.0004 X .970±.002 H06, 6-702456-6, BRASS, PER TE SPEC. 100-86	794223-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 21MAY2003	TE Connectivity	
		CHK C. JONES 21MAY2003		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. JONES 21MAY2003	NAME	SOCKET, MINI UNIVERSAL MATE-N-LOK™2
mm	0 PLC ±	PRODUCT SPEC	SIZE	CAGE CODE DRAWING NO
	1 PLC ±	APPLICATION SPEC	A1	00779 ©=794223
	2 PLC ±	WEIGHT	SCALE	5:1
	3 PLC ±0.30 [.012]	CUSTOMER DRAWING	SHEET	1 OF 1
	4 PLC ±		REV	J2
ANGLES	FINISH			
MATERIAL SEE TABLE	SEE TABLE			