





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J3	ECO-19-006502	30APR2019	AP	WS
	J4	REVISED PER ECN-23-206968	11APR2023	WLS	VS
	J5	REVISED PER ECN-24-279340	22AUG2024	WLS	JP
	K	REVISED PER ECN-25-323497	06JUN2025	WLS	JP



- 1 MATERIAL:
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS.
HOLDDOWNS - PHOSPHOR BRONZE.
 - 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
 - 3 KAPTON VACUUM PICK UP BUTTON.
 - 4 DIMENSION APPLIES TO SOLDERTAIL SURFACES, HOLDDOWNS SURFACES AND STANDOFF SURFACES.
 - 5 ALL SOLDERTAILS AND HOLDDOWNS.
 - 6 PLATING;
CONTACTS - 0.38 μ m MINIMUM GOLD,
OR
0.0762 μ m MINIMUM GOLD FLASH OVER 0.31 μ m MINIMUM PALLADIUM NICKEL,
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,


2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS.

ALL OVER 1.27 μ m MINIMUM NICKEL.

HOLDDOWNS - 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
- 7 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACC. TO NUMBER OF POSITION).
- 8 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

43.04	36.86	40.27	33.00	40.00	24	5-794637-4
40.04	33.86	37.27	30.00	37.00	22	5-794637-2
37.04	30.86	34.27	27.00	34.00	20	5-794637-0
34.04	27.86	31.27	24.00	31.00	18	4-794637-8
31.04	24.86	28.27	21.00	28.00	16	4-794637-6
28.04	21.86	25.27	18.00	25.00	14	4-794637-4
25.04	18.86	22.27	15.00	22.00	12	4-794637-2
22.04	15.86	19.27	12.00	19.00	10	4-794637-0
19.04	12.86	16.27	9.00	16.00	8	3-794637-8
16.04	9.86	13.27	6.00	13.00	6	3-794637-6
13.04	6.86	10.27	3.00	10.00	4	3-794637-4
10.04	3.86	7.27	-	7.00	2	3-794637-2
DIM V	DIM W	DIM Y	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19-MAR-2003 K. WHITAKER CHK 19-MAR-2003 C. JONES APVD 19-MAR-2003 C. JONES		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.20 3 PLC ±. 4 PLC ±. ANGLES ±° FINISH		NAME SMT, VERTICAL, MECH. HOLDDOWN ASSY, 0.38Au or 0.3IPdNi, HEADER DUAL ROW, MICRO MATE-N-LOK TM	
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000		SIZE A200779	
MATERIAL 		WEIGHT -		DRAWING NO C=794637	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 2 REV K	



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 19-MAR-2003
K. WHITAKER
CHK 19-MAR-2003
C. JONES
APVD 19-MAR-2003
C. JONES

PRODUCT SPEC
108-1836
APPLICATION SPEC
114-13000
WEIGHT
-

CUSTOMER DRAWING

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.20
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

NAME
SMT, VERTICAL, MECH. HOLDDOWN ASSY, 0.38Au or 0.31PdNi, HEADER DUAL ROW, MICRO MATE-N-LOK

SIZE
A2

CAGE CODE
b0779

DRAWING NO
C-794637

RESTRICTED TO
-

SCALE
4:1

SHEET
2 OF 2

REV
K

TE Connectivity

1471-9 (3/13)