




THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS					
© COPYRIGHT 20		BY -		CM		53		P	LTR	DESCRIPTION	DATE	DWN	APVD
									D2	REVISED PER ECR-18-006831	12JUN2018	JB	DZ
									D3	ECO-19-006909	03MAY2019	AP	WS
									D4	REVISED PER ECN-22-186748	06DEC2022	WLS	VS
									E	REVISED PER ECN-25-313010	03APR2025	WLS	JP

1 BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.

0.76 μm MIN. THK. GOLD STRIPE,
OR
0.0762μm MIN. THK. GOLD FLASH OVER 0.69μm MIN. THK. PALLADIUM NICKEL

IN THE GOLD STRIP AREA PER TE CONNECTIVITY’S DISCRETION,

2 BRIGHT TIN IN THE CRIMP AREA, OVER NICKEL PLATE.

0.38 THK GOLD STRIPE,
OR
0.0762μm MIN. THK. GOLD FLASH OVER 0.31μm MIN. THK. PALLADIUM NICKEL

IN THE GOLD PLATE AREA PER TE CONNECTIVITY’S DISCRETION,

3 1.5 - 4.0 THK. BRIGHT TIN.

4 WIRE RANGE: 26 - 30 AWG.

5 INSULATION RANGE: 0.89 - 1.524 mm.

1-794607-2	1	1-794611-2
1-794607-1	2	1-794611-1
794607-1	3	794611-1
REELED PN	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	19-OCT-1999	TE Connectivity			
DIMENSIONS:		CHK	19-OCT-1999				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	19-OCT-1999	NAME			
	0 PLC ±	PRODUCT SPEC					
	1 PLC ±	108-1836		CONTACT, RECEPTACLE, CRIMP SNAP-IN, MICRO MATE-N-LOK(TM)			
	2 PLC ±0.20	APPLICATION SPEC					
	3 PLC ±	114-13000		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	4 PLC ±	WEIGHT		A2	00779	C-794611	-
	ANGLES ±1°	CUSTOMER DRAWING		SCALE	10:1	SHEET	OF
MATERIAL	FINISH					REV	E
0.2 PH BRZ	SEE TABLE						