





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	-
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E3	REVISED PER ECN-20-100750	10DEC2020	WLS	VS
	E4	REVISED PER ECN-23-240910	27NOV2023	WLS	VS
	E5	REVISED PER ECN-24-279340	20AUG2024	WLS	JP
	F	REVISED PER ECN-25-323497	04JUN2025	WLS	JP



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP. , NYLON, COLOR BLACK.
CONTACT - BRASS.
- 2 MAXIMUM INSERTION 30 LBS.
- 3 RECOMMENDED BOARD THICKNESS 1.57.
- 4 FINISHING: CONTACT - 0.38 μ m MINIMUM GOLD,
OR
0.0762 μ m MINIMUM GOLD FLASH OVER 0.31 μ m MINIMUM PALLADIUM NICKEL,
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,

2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS.

ALL OVER 1.27 μ m MINIMUM NICKEL.
- 5 CUTTING AREA REGION, NO PLATING IS PRESENT.
- 6 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 7 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	40.00	33.00	36.86	24	5-794631-4
	37.00	30.00	33.86	22	5-794631-2
	OBSOLETE	34.00	27.00	30.86	20
OBSOLETE	31.00	24.00	27.86	18	4-794631-8
	28.00	21.00	24.86	16	4-794631-6
	25.00	18.00	21.86	14	4-794631-4
	22.00	15.00	18.86	12	4-794631-2
	19.00	12.00	15.86	10	4-794631-0
	16.00	9.00	12.86	8	3-794631-8
	13.00	6.00	9.86	6	3-794631-6
	10.00	3.00	6.86	4	3-794631-4
	7.00	-	3.86	2	3-794631-2
	DIM Y	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER		16AUG99		 TE Connectivity			
		CHK K COBLE		16AUG99					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K COBLE		16AUG99		NAME	
		0 PLC ±.		PRODUCT SPEC		VERTICAL HEADER ASSEMBLY, THRU HOLE, 0.38Au or 0.31PdNi DUAL ROW, MICRO MATE-N-LOK™			
		1 PLC ±.		108-1836					
		2 PLC ±0.20		APPLICATION SPEC					
		3 PLC ±.		114-13000		SIZE		CAGE CODE	DRAWING NO
		4 PLC ±.		WEIGHT		A2		00779	G=794631
		ANGLES ±°							
MATERIAL		FINISH							
									
CUSTOMER DRAWING						SCALE		4:1	SHEET
								1	2
								REV	F

