





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT 20 BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F5	REVISED PER ECN-22-160768	24JUN2022	WLS	VS
	F6	REVISED PER ECN-23-240910	29NOV2023	WLS	VS
	F7	REVISED PER ECN-24-279340	30AUG2024	WLS	JP
	G	REVISED PER ECN-25-323497	12JUN2025	WLS	JP



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP. NYLON, COLOR BLACK.
CONTACT - BRASS.
HOLD DOWNS - PHOSPHOR BRONZE.
- 2 MAXIMUM INSERTION 30 LBS.
- 3 RECOMMENDED BOARD THICKNESS 1.57.
- 4 FINISH: CONTACT - 0.38 μ m MINIMUM GOLD,
OR
0.0762 μ m MINIMUM GOLD FLASH OVER 0.31 μ m MINIMUM PALLADIUM NICKEL.
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,

2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS.

ALL OVER 1.27 μ m MINIMUM NICKEL.

HOLDDOWNS - 2.54 μ m MINIMUM MATTE TIN OVER 1.27 MINIMUM NICKEL .
- 5 CUTTING AREA REGION, NO PLATING IS PRESENT.
- 6 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 7 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	40.00	33.00	37.30	36.86	24	5-794681-4
	37.00	30.00	34.30	33.86	22	5-794681-2
	34.00	27.00	31.30	30.86	20	5-794681-0
OBSOLETE	31.00	24.00	28.30	27.86	18	4-794681-8
	28.00	21.00	25.30	24.86	16	4-794681-6
OBSOLETE	25.00	18.00	22.30	21.86	14	4-794681-4
	22.00	15.00	19.30	18.86	12	4-794681-2
	19.00	12.00	16.30	15.86	10	4-794681-0
	16.00	9.00	13.30	12.86	8	3-794681-8
	13.00	6.00	10.30	9.86	6	3-794681-6
	10.00	3.00	7.30	6.86	4	3-794681-4
	7.00	-	4.30	3.86	2	3-794681-2
	DIM A	DIM Z	DIM Y	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 17AUG99 CHK K. COBLE 17AUG99 APVD K. COBLE 17AUG99		 TE Connectivity			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.20 3 PLC ±. 4 PLC ±. ANGLES ±1° FINISH		NAME VERTICAL, HEADER, ASSEMBLY, THRU HOLE, 0.38Au or 0.31PdNi DUAL ROW, MICRO MATE-N-LOK™		SIZE A2	
MATERIAL 		WEIGHT -		CAGE CODE 00779		DRAWING NO C-794681	
		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2	
						REV G	

