





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K4	REVISED PER ECN-23-206968	11APR2023	WLS	VS
	K5	REVISED PER ECN-23-240910	27NOV2023	WLS	VS
	K6	REVISED PER ECN-24-279340	22AUG2024	WLS	JP
	L	REVISED PER ECN-25-323497	11JUN2025	WLS	JP

D



D

C



C

B

- 1 MATERIAL:
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS.
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 KAPTON VACUUM PICK UP BUTTON.
- 4 DIMENSION APPLIES TO SOLDERTAIL SURFACES, HOLDDOWNS SURFACES AND STANDOFF SURFACES.
- 5 ALL SOLDERTAILS AND HOLDDOWNS.
- 6 PLATING:
CONTACTS - 0.76µm MINIMUM GOLD,
OR
0.0762µm MINIMUM GOLD FLASH OVER 0.69µm MINIMUM PALLADIUM NICKEL,
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,
2.54µm MATTE TIN MINIMUM ON SOLDER TAILS.
ALL OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 7 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACC. TO NUMBER OF POSITION).
- 8 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

B

OBSOLETE

OBSOLETE

43.04	36.86	40.27	33.00	40.00	24	5-794638-4
40.04	33.86	37.27	31.00	37.00	22	5-794638-2
37.04	30.86	34.27	27.00	34.00	20	5-794638-0
34.04	27.86	31.27	24.00	31.00	18	4-794638-8
31.04	24.86	28.27	21.00	28.00	16	4-794638-6
28.04	21.86	25.27	18.00	25.00	14	4-794638-4
25.04	18.86	22.27	15.00	22.00	12	4-794638-2
22.04	15.86	19.27	12.00	19.00	10	4-794638-0
19.04	12.86	16.27	9.00	16.00	8	3-794638-8
16.04	9.86	13.27	6.00	13.00	6	3-794638-6
13.04	6.86	10.27	3.00	10.00	4	3-794638-4
10.04	3.86	7.27		7.00	2	3-794638-2
DIM V	DIM W	DIM Y	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER CHK C. JONES APVD C. JONES	19-MAR-2003 19-MAR-2003 19-MAR-2003	TE Connectivity		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	108-1836	NAME SMT, VERTICAL, SMT HOLDDOWN ASSY, 0.76Au or 0.69PdNi, HDR, DUAL ROW, MICRO MATE-N-LOK (TM)		
	0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±1°	APPLICATION SPEC	114-13000	SIZE A2	CAGE CODE 0779	DRAWING NO C-794638
MATERIAL 	FINISH 	WEIGHT	-	RESTRICTED TO	-	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 2	REV L

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B


A

D


C


B

A



KEYING BY POSITION SIZE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19-MAR-2003 K. WHITAKER	 TE Connectivity			
DIMENSIONS:		CHK 19-MAR-2003 C. JONES				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 19-MAR-2003 C. JONES	NAME SMT, VERTICAL, SMT HOLDDOWN ASSY, 0.76Au or 0.69PdNi, HDR, DUAL ROW, MICRO MATE-N-LOK (TM)			
	0 PLC ±	PRODUCT SPEC 108-1836	SIZE		DRAWING NO	
	1 PLC ±	APPLICATION SPEC 114-13000	CAGE CODE		RESTRICTED TO	
MATERIAL	2 PLC ±0.20	WEIGHT -	A260779		C-794638	
	3 PLC ±	CUSTOMER DRAWING	SCALE 4:1		SHEET 2 OF 2	
					REV L	