





P	LTR	DESCRIPTION	DATE	DWN	APVD
	G5	REVISED PER ECN-23-240910	29NOV2023	WLS	VS
	G6	REVISED PER ECN-24-279340	23AUG2024	WLS	JP

D

C

B

A



- 1

MATERIAL;
CONTACTS - BRASS.
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
- 2

RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3

PLATING;
CONTACTS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL ALL OVER.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL ALL OVER.
- 4

COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 5

FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBsolete

36.86	37.30	33.00	40.00	24	5-794677-4
33.86	34.30	30.00	37.00	22	5-794677-2
30.86	31.30	27.00	34.00	20	5-794677-0
27.86	28.30	24.00	31.00	18	4-794677-8
24.86	25.30	21.00	28.00	16	4-794677-6
21.86	22.30	18.00	25.00	14	4-794677-4
18.86	19.30	15.00	22.00	12	4-794677-2
15.86	16.30	12.00	19.00	10	4-794677-0
12.86	13.30	9.00	16.00	8	3-794677-8
9.86	10.30	6.00	13.00	6	3-794677-6
6.86	7.30	3.00	10.00	4	3-794677-4
3.86	4.30	-	7.00	2	3-794677-2
DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER CHK K. COBLE APVD K. COBLE	12AUG99 12AUG99 12AUG99	 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC	±	PRODUCT SPEC	THRU-HOLE, RIGHT ANGLE, TIN HEADER MECHANICAL BOARDLOCK, DUAL ROW, MICRO MATE-N-LOK™			
	1 PLC	±	108-1836				
	2 PLC	±0.20	APPLICATION SPEC				
	3 PLC	±	114-13000				
4 PLC	±	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		FINISH	-	A2	b0779	C-794677	-
		CUSTOMER DRAWING			SCALE	SHEET	REV
					4:1	1 OF 2	G6

D

C

B

A

794677

