




THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G6	REVISED PER ECN-23-240910	29NOV2023	WLS	VS
	G7	REVISED PER ECN-24-256440	14MAR2024	WLS	VS
	G8	REVISED PER ECN-24-279340	23AUG2024	WLS	JP
	H	REVISED PER ECN-25-323497	11JUN2025	WLS	JP



- 1 MATERIAL;
CONTACTS - BRASS.
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 PLATING;
CONTACTS - 0.38 μ m MINIMUM GOLD,
OR
0.0762 μ m MINIMUM GOLD FLASH OVER 0.31 μ m MINIMUM PALLADIUM NICKEL,
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,

2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS.

ALL OVER 1.27 μ m MINIMUM NICKEL.
- HOLDDOWNS - 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE , SEE SPECIFICATION 114-13000.



OBSOLETE	36.86	37.30	33.00	40.00	24	5-794678-4
	33.86	34.30	30.00	37.00	22	5-794678-2
	30.86	31.30	27.00	34.00	20	5-794678-0
	27.86	28.30	24.00	31.00	18	4-794678-8
OBSOLETE	24.86	25.30	21.00	28.00	16	4-794678-6
	21.86	22.30	18.00	25.00	14	4-794678-4
OBSOLETE	18.86	19.30	15.00	22.00	12	4-794678-2
	15.86	16.30	12.00	19.00	10	4-794678-0
OBSOLETE	12.86	13.30	9.00	16.00	8	3-794678-8
	9.86	10.30	6.00	13.00	6	3-794678-6
	6.86	7.30	3.00	10.00	4	3-794678-4
	3.86	4.30	-	7.00	2	3-794678-2
	DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 12AUG99 CHK K. COBLE 12AUG99 APVD K. COBLE 12AUG99		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±1° FINISH		NAME THRU-HOLE, RIGHT ANGLE, HDR MECH. BOARDLOCK, 0.38Au or 0.31PdNi DUAL ROW, MICRO MATE MATE-N-LOK™		SIZE A2	
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000 WEIGHT -		CAGE CODE 00779		DRAWING NO C=794678	
MATERIAL 				RESTRICTED TO -		SCALE 4:1	
CUSTOMER DRAWING				SHEET 1 OF 2		REV H	

