

D

C

B





A

D

C

B

A



- 1

MATERIAL;
CONTACTS - BRASS.
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
- 2

RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3

PLATING;
CONTACTS - 0.76µm MINIMUM GOLD ON MATING AREA.
2.54µm MINIMUM MATTE TIN ON SOLDER TAILS.
ALL OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 4

COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION).
- 5

FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	36.86	37.30	33.00	40.00	24	5-794679-4
OBSOLETE	33.86	34.30	30.00	37.00	22	5-794679-2
OBSOLETE	30.86	31.30	27.00	34.00	20	5-794679-0
OBSOLETE	27.86	28.30	24.00	31.00	18	4-794679-8
OBSOLETE	24.86	25.30	21.00	28.00	16	4-794679-6
	21.86	22.30	18.00	25.00	14	4-794679-4
OBSOLETE	18.86	19.30	15.00	22.00	12	4-794679-2
	15.86	16.30	12.00	19.00	10	4-794679-0
	12.86	13.30	9.00	16.00	8	3-794679-8
	9.86	10.30	6.00	13.00	6	3-794679-6
	6.86	7.30	3.00	10.00	4	3-794679-4
	3.86	4.30	-	7.00	2	3-794679-2
	DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
B. HAYMAKER
CHK
K. COBLE
APVD
K. COBLE
PRODUCT SPEC
108-1836
APPLICATION SPEC
114-13000
WEIGHT
-

12AUG99
12AUG99
12AUG99

TE Connectivity

NAME
THRU-HOLE, RIGHT ANGLE, 30 GOLD
HEADER, MECHANICAL BOARDLOCK,
DUAL ROW, MICRO MATE-N-LOK™

SIZE
A260779

CAGE CODE
C-794679

DRAWING NO
-

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
4:1

SHEET
1

OF
2

REV
G7

794679

