




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F5	REVISED PER ECN-22-160768	24JUN2022	WLS	VS
	F6	REVISED PER ECN-23-240910	29NOV2023	WLS	VS
	F7	REVISED PER ECN-24-279340	30AUG2024	WLS	JP



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP. NYLON, COLOR BLACK.
CONTACT - BRASS.
HOLD DOWNS - PHOSPHOR BRONZE.
 - 2 MAXIMUM INSERTION 30 LBS.
 - 3 RECOMMENDED BOARD THICKNESS 1.57.
 - 4 FINISH: CONTACT - 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
HOLDDOWN - 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
 - 5 ABSENT COMPONENT IN THIS SIDE ONLY.
 - 6 CUTTING AREA REGION, NO PLATING IS PRESENT.
- 7 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION.
- 8 FOR REELLING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	40.00	33.00	37.30	36.86	24	5-794680-4
	37.00	30.00	34.30	33.86	22	5-794680-2
OBSOLETE	34.00	27.00	31.30	30.86	20	5-794680-0
	31.00	24.00	28.30	27.86	18	4-794680-8
	28.00	21.00	25.30	24.86	16	4-794680-6
	25.00	18.00	22.30	21.86	14	5 4-794680-5
	25.00	18.00	22.30	21.86	14	4-794680-4
	22.00	15.00	19.30	18.86	12	4-794680-2
	19.00	12.00	16.30	15.86	10	4-794680-0
	16.00	9.00	13.30	12.86	8	3-794680-8
	13.00	6.00	10.30	9.86	6	3-794680-6
	10.00	3.00	7.30	6.86	4	3-794680-4
	7.00	-	4.30	3.86	2	3-794680-2
	DIM A	DIM Z	DIM Y	DIM X	NO. OF POSN.	ASSEMBLY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 23-MAR-2005 CHK S. HOOPER 23-MAR-2005 C. JONES APVD 23-MAR-2005 C. JONES		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.20 3 PLC ±. 4 PLC ±. ANGLES ±° FINISH		NAME VERTICAL HEADER ASSEMBLY, THRU HOLE, TIN, DUAL ROW, MICRO MATE-N-LOK(TM)			
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000		SIZE A2		CAGE CODE 00779	
MATERIAL 				DRAWING NO C-794680		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 2	
						REV F7	

