


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	PART OBSOLESCENCE	01JUL2024	RS	VG

POS.	L±0.5	PART NO.
1	2.54	825434 -1
2	5.08	-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	-0
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1-
15	38.10	1-
16	40.64	1-
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	2-
21	53.34	2-
22	55.88	2-
23	58.42	2-
24	60.96	2-
25	63.50	2-
26	66.04	2-
27	68.58	2-
28	71.12	2-
29	73.66	2-
30	76.20	3-
31	78.74	3-
32	81.28	3-
33	83.82	3-
34	86.36	3-
35	88.90	3-
36	91.44	3-
37	93.98	3-
38	96.52	3-
39	99.06	3-
40	101.60	4-
41	104.14	4-
42	106.68	4-
43	109.22	4-
44	111.76	4-
45	114.30	4-
46	116.84	4-
47	119.38	4-
48	121.92	4-
49	124.46	4-
50	127.00	5- 825434 -0



- 1 MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au plating OVER Min 1.27µm Ni)
SOLDER SIDE: 3.0-5.0µm TIN OVER Min 1.27µm NICKEL

2 OBSOLETE

CONTACT PIN	CuZn	△
PIN HOUSEING	PBT GV	GREEN
DESCRIPTION	MATERIAL	SURFACE COLOR


DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.2mm

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -



DWN

A.HO

11APR1984

CHK

M.SCHAARSCHMIDT

11APR1984

APVD

-

PRODUCT SPEC

108-18012

APPLICATION SPEC

-

WEIGHT

-

MATERIAL

-

FINISH

-



TE Connectivity

NAME

AMPMODU II PIN HEADER, SINGLE ROW

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-825434

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV F2